

City of Madison

Proposed Rezoning

Location 702-750 University Row Applicant U.W. Health/Dan Day -D'Onofrio Kotke & Associates


From: PD(GDP)

To: PD(SIP)


Existing Use Vacant land at Union Corners

Proposed Use Construct temporary surface parking lot at University Crossing (Lots 2 and 3)

Public Hearing Date
Plan Commission
21 September 2015
Common Council
06 October 2015



For Questions Contact: Tim Parks at: 261-9632 or tparks@cityofmadison.com or City Planning at 266-4635




Scale: 1'' = 400'

City of Madison, Planning Division: RPJ: Date: 14 September 2015



City of Madison



Date of Aerial Photography: Spring 2013



LAND USE APPLICATION

CITY OF MADISON

215 Martin Luther King Jr. Blvd; Room LL-100 PO Box 2985: Madison, Wisconsin 53701-2985

FOR OFFI	ICE USE ONLY:
Amt. Paid	Receipt No
Date Received	
Received By	
Parcel No	
Aldermanic District	(
Zoning District	
Special Requirements	
Review Required By:	
Urban Design Commission	on Plan Commission
Common Council	Other:

Phone: 608.266.4635 Facsimile: 608.267.8739	Pate Received				
All Land Use Applications should be filed with the Zoning	Parcel No				
Administrator at the above address.	Aldermanic District				
The following information is required for all applications for Plan	Zoning District				
Commission review except subdivisions or land divisions, which	Special Requirements				
should be filed using the Subdivision Application.	Review Required By:				
This form may also be completed online at:	Urban Design Commission Plan Commission				
$\underline{www.cityofmadison.com/developmentcenter/landdevelopment}$	Common Council Other:				
	Form Effective: February 21, 2013				
L. Project Address: 750 University Row					
Project Title (if any): U.W. Health, Outlot 2 & 3, Parking Lots					
2. This is an application for (Check all that apply to your Land	Use Application):				
X Zoning Map Amendment fromGDP	to				
☐ Major Amendment to Approved PD-GDP Zoning ☐	Major Amendment to Approved PD-SIP Zoning				
☐ Review of Alteration to Planned Development (By Plan Com	nmission)				
☐ Conditional Use, or Major Alteration to an Approved Condit	ional Use				
☐ Demolition Permit					
Other Requests:	·				
3. Applicant, Agent & Property Owner Information:	HW Hashin HW Hashin 200				
	ny: U.W. Health - U.W. Hospital & Clinics				
treet Address: 600 N. Highland Ave City/State:	Madison, WI Zip: <u>53792</u>				
elephone: (608) 263 - 9160 Fax: ()	Email: ahowick@uwhealth.org				
roject Contact Person: Dan Day Compar	ny: D' Onofrio, Kottke & Associates				
treet Address: 7553 Westward Way City/State:	Madison, WI zip: 53717				
elephone: (<u>608</u>) <u>833 - 7530</u> Fax: ()	Email:				
roperty Owner (if not applicant): U.W. Health					
	Zip:				
. Project Information:					
rovide a brief description of the project and all proposed uses of the	e site:Temporary commuter surface parking lots.				
Development Schedule: Commencement October 2015	Completion Partial - November 2015				
	Final - June 2016				

5. Required Submittal Information

All Land Use applications are required to include the following:

X Project Plans including:*

Name of Applicant

Authorizing Signature of Property Owner

- Site Plans (<u>fully dimensioned</u> plans depicting project details including all lot lines and property setbacks to buildings; demolished/proposed/altered buildings; parking stalls, driveways, sidewalks, location of existing/proposed signage; HVAC/Utility location and screening details; useable open space; and other physical improvements on a property)
- Grading and Utility Plans (existing and proposed)
- Landscape Plan (including planting schedule depicting species name and planting size)
- Building Elevation Drawings (fully dimensioned drawings for all building sides, labeling primary exterior materials)
- Floor Plans (fully dimensioned plans including interior wall and room location)

Provide collated project plan sets as follows:

- Seven (7) copies of a full-sized plan set drawn to a scale of 1 inch = 20 feet (folded or rolled and stapled)
- Twenty Five (25) copies of the plan set reduced to fit onto 11 X 17-inch paper (folded and stapled)
- One (1) copy of the plan set reduced to fit onto 8 ½ X 11-inch paper
- * For projects requiring review by the **Urban Design Commission**, provide **Fourteen** (14) additional 11x17 copies of the plan set. In addition to the above information, <u>all</u> plan sets should also include: 1) Colored elevation drawings with shadow lines and a list of exterior building materials/colors; 2) Existing/proposed lighting with photometric plan & fixture cutsheet; and 3) Contextual site plan information including photographs and layout of adjacent buildings and structures. The applicant shall <u>bring</u> samples of exterior building materials and color scheme to the Urban Design Commission meeting.

Х	Letter of Intent: Provide one (1) Copy p	er Plan Set describing this applicat	tion in detail including, but not limited to:
	 Project Team Existing Conditions Project Schedule Proposed Uses (and ft² of each) Hours of Operation 	 Building Square Footage Number of Dwelling Units Auto and Bike Parking Stalls Lot Coverage & Usable Oper Space Calculations 	
X	Filing Fee: Refer to the Land Use Applica	ation Instructions & Fee Schedule. I	Make checks payable to: City Treasurer.
X			s submitted in hard copy with their application as n their application materials, or by e-mail to
	Additional Information may be require	d, depending on application. Refer	to the <u>Supplemental Submittal Requirements.</u>
6.	Applicant Declarations		
X		ons <u>in writing</u> no later than <u>30</u>	cant notify the district alder and any nearby days prior to FILING this request. List the AND the dates you sent the notices:
	→ If a waiver has been granted to this	requirement, please attach any o	correspondence to this effect to this form.
X			ation, the applicant is required to discuss the ivision staff; note staff persons and date.
	Planning Staff:Tim Parks	Date: 7/16/2015 Zoning Staff:	Matt Tucker Date: 7/16/2015

Relationship to Property: U.W. Health Director of Facilities Planning

The applicant attests that this form is accurately completed and all required materials are submitted:

Andrew Howigk



Letter of Intent

Temporary Commuter Parking at University Crossing 750 University Row

UW Health – Hospitals and Clinics August 4, 2015

Project Description

UW Hospital would like to build a temporary commuter parking lot at University Crossing to replace the 300 commuter parking stalls currently leased at the Hill Farms State Office site. These stalls are used by the Hospital staff and are critical to the operation. These stalls provide an affordable alternative to the higher priced structured parking on the Hospital campus. The proposed surface parking lots for 300 cars at the UW Health sites at University Crossing are temporary until the site is developed, which is anticipated over the next five years. At that time the additional parking will be incorporated into the design of future parking structures and taken through the PUD/SIP city approval process.

We ask that the landscaping requirements and bike parking requirements for the parking lots be waved since these will be temporary lots and require minimal investment in infrastructure cost. Current bike parking is available at the UW Health Digestive Health Center. This includes 15 B-Cycles, 8 indoor and 4 outdoor bike parking stalls.

Site lighting for the project will be provided for safety reasons and will meet city ordinances for light trespass and dark sky.

Parking ratios on this master planned site are low due to shared parking between the apartments and the office buildings. The current master plan has a parking ratio of 2.69 to 2.79. With the additional 300 stalls the parking ratio at proposed full build-out would be 3.24 to 3.37/1000 GSF.

Current traffic patterns should not change significantly since the 300 stalls exist today at the Hill Farm site which is a few blocks away from the University Crossing site.

This site has an adopted storm water management plan that was approved with the plat of University Crossing. The impervious areas that come from the parking lots and structured parking are intended to go to the existing grit filtration system and bioretention basin on the west side of the University Crossing site. The areas being proposed with these parking areas is very similar to the areas assumed in the storm report. If the final design results in additional area we will be implementing an additional bioretention system to account for the differential.

Erosion control during construction will be a key component to the implementation of plan. We will be proposing erosion control features that will go above and beyond the ordinances of the City of Madison.

Project Schedule

Proposed schedule of construction for the parking lots will take place from October to December with final finish course, final seeding and final erosion control in May and June of 2016.

Hours of Operation

Anticipated hours of use are from 5:00 am until 10:00 pm.

Estimated Project Cost:

\$800,000

Site Area Calculations

64,458 sf
40 000 -4
<u>43,005 sf</u>
07,463 sf
89,751 sf
17,712 sf

Project Team

UW Health Andrew Howick and Mike Grady
Krupp Construction Paul Lenhart and Dietmar Bassuner
D'Onofrio Kottke & Assoc. Dan Day
Potter Lawson Inc. Doug Hursh

→ SITE LOCATION















Lot #	Potential Land Use	Net Lot Area (sf)	Proposed I Area		Proposed Height (stories)		uilding Area sf)	F.A.R.	Proposed Park	ing Stalls
									Surface:	47
			Bldg 1:	20,000		Bldg 1:	67,420		Structure A:	456
1	Clinic	186,000	Bldg 1A:	17,500	4	Bldg 1A:	70,000	0.74	Below Bldg:	28
		5							Surface:	19
_	Oli-t-								Structure B:	342
2	Clinic	144,184	Bldg 2:	26,700	3	Bldg 2:	80,000	0.55	Below Bldg:	50
3	Non-profit hospitality	43,560	Bldg 3:	13,400	3	Bldg 3:	40,000	0.92	Surface:	42
4	Office/Retail	54,014	Bldg 4:	22,800	3	Bldg 4:	64,940	1.2	Surface: Below Bldg:	29 35
	Hotel						84,000 (or	2.10 (or	Surface:	36
5	(or Office)	40,075	Bldg 5:	14,000	6 (or 4)	Bldg 5:	64,000)	1.60)	Below Bldg:	24
	Residential +		Residential	24,234		Residential	131,810			(8)
6	Parking C	68,000	Parking	32,315	4 & 5	Parking	139,690	1.94		337

Total Building Area: 538,170

Total Parking Stalls 1,445

(or 518,170 w./ #5 Office)

2.69 stalls/ 1,000 sf (or 2.79 w./ #5 Office)

*Parking Structure C for Buildings 4, 5, & 6

Parking

Parking Structure A: 3 Levels - approx. 456 stalls Parking Structure B: 3 Levels - approx. 342 stalls Parking Structure C: 3 Levels - approx. 337 stalls (Parking Structures to be 10-11 feet floor to floor)



**This is a Concept Masterplan. Final building footprint uses and sizes will be determined during the SIP submittals.
































UNIVERSITY CROSSING - LOTS 2 & 3

CITY OF MADISON DANE COUNTY, WISCONSIN



PROJECT LOCATION

INDEX OF SHEETS

TS-001 COVER SHEET

C-101 EXISTING CONDITIONS

C-102 SITE PLAN

C-103 SITE GRADING AND EROSION CONTROL

-104 DETAILS

E-100 ELECTRICAL SITE PLAN

E-101 PHOTOMETRIC SITE PLAN .5 FC TRESPASSING LEVEL

MARKED WITH CONTOUR LINE

D'ONOFRIO KOTTKE AND ASSOCIATES, INC.

7530 Westward Way, Madison, WI 53717 Phone: 608.833.7530 • Fax: 608.833.1089 YOUR NATURAL RESOURCE FOR LAND DEVELOPMENT

> DATE: 08-05-15 REVISED:


9

DRAWN BY: JMS


FN: 15-05-131
Sheet Number:

TS-001


File: U:\User\1505131\Drawings\Cover.dwg Layout 1 User: ishapiro Plotted: Aug 04, 2015 - 6:01pm



File: U:\User\1505131\Drawings\Existing Conditions.dwg Existing User: jshapiro Plotted: Aug 04, 2015 - 6:04pm



File: U:\User\1505131\Drawings\Site Plan.dwg Site Plan User: jshapiro Plotted: Aug 04, 2015 - 6:08pm



8. INSTALL INLET PROTECTION IN ALL STORM SEWER INLETS AND CATCH BASINS THAT MAY RECEIVE RUNOFF FROM DISTURBED AREAS

File: U:\User\1505131\Drawings\Site Plan.dwg Grading Plan_User. jshapiro_Plotted: Aug 04, 2015 - 6:09pm

Q 0 **2012** CROSSING

UNIVERSITY

SCALE: 1"= 60' (PAGE SIZE: 11x17)


DATE: 08-05-15


DRAWN BY: JMS


FN: 15-05-131


C-103

16. DEWATERING, IF APPLICABLE, SHALL BE CONDUCTED PER WONR STORM WATER MANAGEMENT TECHNICAL STANDARD 1061.










 φ 0 UNIVERSITY CROSSING - LOTS DATE: 08-05-15 REVISED:

FN: 15-05-131

C-104

File: U:\Usen\1505131\Drawings\Site Plan.dwg Details User: jshapiro Plotted: Aug 04, 2015 - 6:09pm



BUILDERS

W133 N5030 Campbell Drive Menomonee Falls, WI 53051

Tailing Address • P.O. Box 91 Butler, WI 53007-0917

Phone • 262-781-8230 Fax • 262-781-1680 affelectric @ staffelectric.co


PROJECT TILLE:
UWHC OFFICES @
UNIVERSITY CROSSING
PARKING EXPANSION
PROJECT LOCATION:
MADISON, WI

SHEET TITLE:
ELECTRICAL SITE PLAN

08/04/2015 DRAWN BY:

APPROVED BY:

SHEET NUMBER



CALCULATION	SUMMARY					
GRID HEIGHT	GROUP	AVE	MAX	MIN	MAX/MIN	AVE/MIN
At Grade	<+> MISC <*> UPPER LOT <#> LOWER LOT	0.36 1.99 1.76	2.95 3.58 3.62	0.01 0.64 0.72	300.50 5.62 5.06	37.13 3.11 2.46

TYPE		LAMP	LUMENS	MOUNTING	LLF	QTY
Pi	McGraw-Edison Talon LED (2) TLM-B06-LED-E1-5WQ-BK	149w LED	13267	25' POLE 2' BASE	0.95	7
P2	McGraw-Edison Talon LED (1) TLM-B06-LED-E1-T4-BK	149w LED	12325	25' POLE 2' BASE	0.95	4
P3	McGraw-Edison Talon LED (1) TLM-B06-LED-E1-T3-BK	149w LED	12375	25' POLE 2' BASE	0.95	1

SITE PLAN - PHOTOMETRIC W/ 5 fc TRESPASSING CONTOUR LINE SCALE: 1' = 30'-0'





BUILDERS

W133 N5030 Campbell Drive Menomonee Falls, WI 53051

Mailing Address • P.O. Box 91

Phone • 262-781-8230 Fax • 262-781-1680 staffelectric @ staffelectric.c

PROJECT TITLE:

UWHC OFFICES @
UNIVERSITY CROSSING
PARKING EXPANSION
PROJECT LOCATION:
MADISON, WI

E: COMETRIC SITE PLAN RESPASSING LEVEL MARKED I CONTOUR LINE

SHEET TITL	PHOI	.5 fc T	WITH	
1.				
2.				
3.				
4.				
5.				
6.				
DA7	re :			08/04/20

DRAWN BY -NRH

APPROVED BY: SCALE: 1" = 30'-0"

SHEET NUMBER

Job Name:

UW Digestive Health - FINAL BOM Architect: Klein Lighting Design (Milwaukee)
Enterprise Ligh Contractor: Staff Electric (Butler) Catalog Number: TLM-B06-LED-E1-T3-BK

Notes:

Type:

OALED

ELL12-26394

DESCRIPTION

The Talon is the most versatile, functionally designed, universally adaptable outdoor luminaire available. Incorporating modular LED LightBAR™ technology, Talon brings outstanding uniformity and energyconscious illumination to walkways, parking lots, roadways, building areas, and any security lighting application. UL/cUL listed for wet locations.

McGRAW-EDISON®



Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

Construction

One-piece heavy-wall, die-cast aluminum construction with integral reveal channels along top surface of housing. Optimized for reliable operation from 40°C down to -30°C, internal cast-in wall separates optical and electrical chambers allowing components to operate cooler. Stainless steel latches and hinges allow for toolless opening and removal of door frame.

Optics

Choice of thirteen (13) patented, high-efficiency AccuLED Optics manufactured from injectionmolded acrylic. Optics are precisely designed to shape the distribution maximizing efficiency and application spacing. AccuLED optics create consistent distributions with the scalability to meet customized application requirements. Talon optics feature quick disconnect wiring plugs and are field-rotatable in 90° increments allowing manipulation of distribution independent of fixture position. Offered standard in 4000K (+/- 275K) CCT and nominal 70 CRI.

Electrical

Offered standard with LED drivers and related electrical componentry hard mounted to die-cast housing details for optimal heat transfer and operating efficiency. Talon operates from 120-277V 50/60Hz, 347V 60Hz, 480V 60Hz. Optional galvanized steel swing-down power tray with integral handle allow tray to be removed from housing providing ample hand and tool room for attachment of fixture during installation. Offered standard with the Cooper Lighting proprietary circuit module designed to withstand 10kV transient line surge, 50,000+ hour life with >70% lumen maintenance. LightBARs™ feature an IP66 enclosure rating.


Mounting

Extruded 8" aluminum arm includes internal bolt guides allowing for easy positioning of fixture during installation to pole or wall surface. Standard single carton packaging of housing, square pole arm and round pole adapter for contractor-friendly arrival of product on site. Optional mounting methods include a wall

mount plate, an external mast arm that accepts 2-3/8" O.D. horizontal tenons and direct mounting to pole or wall surfaces. Tenon adapters available to slipfit over poles equipped with 2-3/8" or 3-1/2" O.D. tenon. 3G vibration rated.

Housing and arm finished in a 5-stage Super TGIC polyester powder coat paint, 2.5 mil nominal thickness for superior protection against fade and wear. Standard colors include black, bronze, grey, white, dark platinum, and graphite metallic. RAL and custom color matches available. Consult the McGraw-Edison Architectural Colors brochure for the complete selection.

Warranty Talon LED features a five-year limited warranty.




TALON MEDIUM LED

2 - 6 LightBARs Solid State LED

ARCHITECTURAL AREA LUMINAIRE


SustainabL&Design

DIMENSIONS




ARM DRILLING

TYPE "M



WALL MOUNT



CERTIFICATION DATA

UL/cUL Listed LM79 / LM80 Compliant IP66 LightBARs 3G Vibration Rated ARRA Compliant ISO 9001

ENERGY DATA

Electronic LED Driver >0.9 Power Factor <20% Total Harmonic Distortion 120-277V/50 & 60hz, 347V/60hz, 480V/60hz -30°C Minimum Temperature 40°C Ambient Temperature Rating

EPA

Effective Projected Area: (Sq. Ft.) Luminaire w/o Arm: 0.79 8" Arm: 0.43

SHIPPING DATA Approximate Net Weight: 42 lbs. (25.91 kgs.)



ADH092070 pc 2011-08-28 14:21:34



Job Name:

UW Digestive Health - FINAL BOM Architect: Klein Lighting Design (Milwaukee) Enterprise Ligh Contractor: Staff Electric (Butler)

Catalog Number: TLM-B06-LED-E1-T3-BK

Notes:

Type:

OALED

ELL12-26394

TLM TALON MEDIUM LED

POWER AND LUMENS BY BAR COUNT


NI	DISTRIBUTION														
Number of LightBARs	Power [Watts]	Current @ 120V [A]	Current @ 277V [A]	T2	Т3	T3S	T4	SL2	SL3	SL4	5MQ	5WQ	5XQ	RW	SLR/SLL
			,			71	ED LIGHT	BAR					U-		
C02	54	0.46	0.21	3,509	3,469	3,391	3,495	3,484	3,368	3,347	3,711	3,724	3,605	3,540	3,203
C03	77	0.65	0.29	5,291	5,230	5,112	5,269	5,252	5,078	5,046	5,594	5,614	5,436	5,337	4,829
C04	101	0.86	0.37	6,983	6,902	6,747	6,954	6,932	6,703	6,660	7,383	7,410	7,174	7,043	6,373
C05	131	1.11	0.50	8,362	8,265	8,079	8,327	8,300	8,026	7,975	8,841	8,872	8,590	8,434	7,631
C06	154	1.30	0.58	10,119	10,002	9,777	10,077	10,045	9,712	9,651	10,699	10,737	10,396	10,206	9,235
						21	LED LIGHT	BAR							***************************************
B02	51	0.43	0.20	4,317	4,267	4,171	4,299	4,285	4,143	4,117	4,564	4,580	4,435	4,354	3,940
B03	73	0.62	0.28	6,508	6,433	6,288	6,481	6,460	6,246	6,207	6,881	6,906	6,686	6,564	5,939
B04	95	0.81	0.35	8,589	8,490	8,299	8,554	8,526	8,244	8,192	9,081	9,114	8,824	8,663	7,839
B05	124	1.05	0.48	10,285	10,166	9,938	10,242	10,209	9,871	9,809	10,874	10,913	10,566	10,373	9,386
B06	146	1.24	0.56	12,446	12,302	12,026	12,395	12,355	11,946	11,871	13,159	13,207	12,786	12,554	11,359

LUMEN MULTIPLIER

Ambient Temperature	Lumen Multiplier
10°C	1.04
15°C	1.03
25°C	1.00
40°C	0.96

ORDERING INFORMATION

SAMPLE NUMBER: TLM-B03-LED-E1-T3-BK



Photocontrol Receptacle
PT=Electrical Power Tray 2L=Bi-Level Switching Capable 7 7060=70 CRI/6000K CCT 8 8030=80 CRI/3000K CCT 8 LCF=LightBAR Cover Plate Matches Housing Finish WM=Wall Mount with Arm DM=Direct Mount for Round or Square Pole DW=Direct Wall Mount MS=External Mast Arm Adapter Battery Pack (Specify 120V or 277V) 6,9

P=Button Type Photocontrol (120V, 208, 240, or 277V) ⁶ R=NEMA Twistlock

Options 5

Accessories 10 MA1010-XX=Single Tenon Adapter for 3 1/2" O.D. Tenon MA1011-XX=2@180° Tenon Adapter for 3 1/2" O.D. Tenon MA1012-XX=3@120° Tenon Adapter for 3 1/2" O.D. Tenon MA1013-XX=4@90° Tenon Adapter for 3 1/2" O.D. Tenon for 3 1/2" O.D. Tenon
MA1014-XX=2@90" Tenon Adapter
for 3 1/2" O.D. Tenon
MA1015-XX=2@120" Tenon Adapter
for 3 1/2" O.D. Tenon
MA1016-XX=3@90" Tenon Adapter for 3 1/2" O.D. Tenon MA1017-XX=Single Tenon Adapter for 2 3/8" O.D. Tenon MA1018-XX=2@180° Tenon Adapter for 2 3/8" O.D. Tenon MA1019-XX=3@120° Tenon Adapter for 2 3/8" O.D. Tenon MA1045-XX=4@90° Tenon Adapter MA1049-XX=4@90* Tenon Adapter for 2 3/8" O.D. Tenon MA1048-XX=2@90* Tenon Adapter for 2 3/8" O.D. Tenon MA1049-XX=3@90* Tenon Adapter for 2 3/8" O.D. Tenon OA/RA1016=NEMA Twistlock Photocontrol - Multi-Tap
OA/RA1027=NEMA Twistlock Photocontrol - 480V OA/RA1201=NEMA Twistlock Photocontrol - 347V OA/RA1013=Shorting Cap MA1253=10kV Circuit Module

- 8 arm and round pole adapter included with fixture.
 2 71 LED LightBAR powered at \$50mA, 7 LED LightBAR powered 3 \$50mA, 7 LED LightBAR powered 3 \$51mAg and \$4000K CCT and nominal 70CM.
 4 Custom and RAL color matching available upon request.
 5 Consult Cooper Lighting Representative for further information.
 5 Add as suffix.

- 5 Add as suffix.
 6 Must specify voltage.
 7 Low-Level output varies by bar count specified. Consult Factory.
 8 Consult Factory for lead times and lumen multiplier.
 9 Available with 802 or C02, 803 or C03, and 804 or C04 configurations only. Rated for 25 Degrees 5 ambient.
 10 Order separately, replace XX with color suffix.

MOUNTING CONFIGURATIONS

Arm Mount 2 @ 180° EPA 2.44 Wall Mount Arm Mount Sing EPA 1.22



Arm Mount 2 @ 90° EPA 2.44

GM=Graphite Metallic WH=White



Arm Mount 3 @ 120° (Round Pole Only) EPA 3.23



Arm Mount 4 @ 90° EPA 3.63

Replacement















COOPER LIGHTING

	CONTRACTOR STATEMENT CONTRACTOR OF THE CONTRACTO	CONTRACTOR DESCRIPTION OF THE PROPERTY OF THE	
			8
	2,535,000		8
	The second secon		8
CONTRACTOR OF THE PARTY OF THE			•
Sec. Name of the least of		****	8
			,
			9
			8
	The state of the s		â
	THE PROPERTY OF THE PARTY OF TH		ş
			3
			ŝ
2102 250 07 TO 100 00 00 00 00 00 00 00 00 00 00 00 00			
900000000000000000000000000000000000000			1
		- Francisco	1
500000000000000000000000000000000000000			1
			1
			1
# 100 miles			3
			6
S0000000000000000000000000000000000000			
The state of the s			
700000			
	SA- November		

SSS SQUARE STRAIGHT STEEL

Catalog #	Туре
Project	
Comments	Date
Prepared by	


- ASTM Grade steel base plate with ASTM A366 base cover
- Hand hole assembly 3" x 5" on 5" and 6" pole; and 2" x 4" on 4" pole
- 10'-39' mounting heights
- Drilled or tenon (specify)

ORDERING INFORMATION

SAMPLE NUMBER: SSS5A20SFM1XG

Product Family	Shaft Size (Inches) ¹	Wall Thickness (Inches)	Mounting Height (Feet)	Base Type	Finish	Mounting Type	Number and Location of Arms	Arm Lengths (Feet)	Options (Add as Suffix)
SSS=Square Straight Steel	4=4° 5=5° 6=6"	A=0.120" M=0.188" X=0.250"	10=10' 15=15' 20=20' 25=25' 30=30' 35=35' 39=39'	S=Square Steel Base	F=Dark Bronze G=Galvanized Steel J=Summit White K=Carbon Bronze L=Dark Platinum P=Primer Powder Coat R=Hartford Green S=Silver T=Graphite Metallic V=Grey W=White X=Custom Color Y=Black	2=2-3/8" O.D. Tenon (4" Long) 3=3-1/2" O.D. Tenon (5" Long) 4=4" O.D. Tenon (6" Long) 5=3" O.D. Tenon (6" Long) 6=2-3/8" O.D. Tenon (6" Long) 7=4" O.D. Tenon (10" Long) A=Type A Drilling C=Type C Drilling E=Type F Drilling F=Type F Drilling G=Type G Drilling J=Type J Drilling M=Type K Drilling M=Type K Drilling R=Type R Drilling S=Type R Drilling T=Type R Drilling T=Type R Drilling T=Type R Drilling T=Type R Drilling	1=Single 2=2 at 180° 3=Triple² 4=4 at 90° 5=2 at 90° X=None	X=None	A=1/2"Tapped Hub (Specify location desired) B=3/4"Tapped Hub (Specify location desired) C=Convenience Outlet ³ E=GFCI Convenience Outlet ³ G=Ground Lug H=Additional Hand Hole ⁴ L=Drilled for Bumper Glitter V=Vibration Dampener

NOTES: 1. All shaft sizes nominal. 2. Square poles are 3 at 90°, round poles are 3 at 120°. 3. Outlet is located 4' above base and on same side of pole as hand hole, unless specified otherwise. Receptacle not included, provision only. 4. Additional hand hole is located 12" below pole top and 90° from standard hand hole location, unless otherwise specified.



WARNING: The use of unauthorized accessories such as banners, signs, cameras or pennants for which the pole was not designed voids the pole warranty from Eaton's Cooper Lighting business and may result in pole failure causing serious injury or property damage. Upon request, Eaton's Cooper Lighting business will supply information regarding total loading capacity. The pole warranty from Eaton's Cooper Lighting business is void unless poles are used and installed as a complete pole/luminaire combination. This warranty specifically excludes failure as the result of a third party act or omission, misuse, unanticipated uses, fatigue failure or similar phenomena resulting from induced vibration, harmonic oscillation or resonance associated with movement of air currents around the product.

Specifications and dimensions subject to change without notice. Consult your Eaton's Cooper Lighting business representative or visit www.cooperlighting.com for available options, accessories and ordering information.

Effective Projected Area (At PoleTop)

Mounting Height (Feet)	Catalog Number ^{1, 2}	Wall Thickness (inches)	Base Square ³ (Inches)	Bolt Circle Diameter (Inches)	Anchor Bolt Projection ³ (Inches)	Shaft Size ³ (Inches)	Anchor Bolt Diameter x Length x Hook (Inches)	Net Weight (Pounds)	Maxin	Maximum Effective Projected Area (Square Feet) ⁴			
			s	вс	BP	В	DxABxH		80 mph	90 mph	100 mph	110 mph	
10	SSS4A10S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	85	30.0	22.0	17.0	13.0	100
15	SSS4A15S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	118	15.0	11.5	8.7	6.5	100
20	SSS4A20S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	150	8.7	5.9	3.9	2.5	150
20	SSS5A20S	0.120	10-1/2	11	4-1/2	5	3/4 x 25 x 3	183	15.4	11.1	7.9	5.5	150
25	SSS4A25S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	181	3.7	1.7	0.3	-	200
25	SSS5A25S	0.120	10-1/2	11	5	5	3/4 x 25 x 3	222	9.3	6.0	3.5	1.6	200
25	SSS6A25S	0.120	12-1/2	12-1/2	5	6	1 x 36 x 4	284	9.9	6.1	3.5	1.2	200
30	SSS5A30S	0.120	10-1/2	11	4-1/2	5	3/4 x 25 x 3	260	4.7	2.1			200
30	SSS5M30S	0.188	10-1/2	11	4-1/2	5	3/4 x 25 x 3	392	10.4	6.4	3.5	1.5	200
30	SSS6A30S	0.120	12-1/2	12-1/2	5	6	1 x 36 x 4	330	4.3	1.4			200
30	SSS6M30S	0.188	12-1/2	12-1/2	5	6	1 x 36 x 4	489	19.0	13.0	8.7	5.6	200
35	SSS5M35S	0.188	10-1/2	11	4-1/2	5	3/4 x 25 x 3	453	5.8	2.8			200
35	SSS6M35S	0.188	12-1/2	12-1/2	5	6	1 x 36 x 4	564	12.8	7.2	3.7	1.0	200
35	SSS6X35S	0.250	12-1/2	12-1/2	5	6	1 x 36 x 4	738	16.5	11.0	6.8	3.5	200
39	SSS6M39S	0.188	12-1/2	12-1/2	5	6	1 x 36 x 4	618	7.3	3.0			300
39	SSS6X39S	0.250	12-1/2	12-1/2	5	6	1 x 36 x 4	816	13.0	7.0	3.7	0.8	300

Effective Projected Area (Two Feet Above Pole Top)

Mounting Height (Feet)	Catalog Number 1,2		Base Square ^a (Inches)	Bolt Circle Diameter (Inches)	Anchor Bolt Projection ³ (Inches)	Shaft Size ³ (Inches)	Anchor Bolt Diameter x Length x Hook (Inches)	Net Weight (Pounds)	Maximum Effective Projected Area (Square Feet) ⁴				Max. Fixture Load - Includes Bracket (Pounds)
									80 mph	90 mph	100 mph	110 mph	A SACTOR AND SACTOR
10	SSS4A10S	0.120	10-1/2	11-	4-1/2	4	3/4 x 25 x 3	85	23.0	17.5	14.0	11.0	100
15	SSS4A15S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	118	13.4	10.0	7.5	5.7	100
20	SSS4A20S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	150	7.6	5.2	3.4	2.1	150
20	SSS5A20S	0.120	10-1/2	11	4-1/2	5	3/4 x 25 x 3	183	13.8	9.9	7.1	4.9	150
25	SSS4A25S	0.120	10-1/2	11	4-1/2	4	3/4 x 25 x 3	181	3.4	1.6	0.3	-	200
25	SSS5A25S	0.120	10-1/2	11	5	5	3/4 x 25 x 3	222	8.5	5.5	3.2	1.5	200
25	SSS6A25S	0.120	12-1/2	12-1/2	5	6	1 x 36 x 4	284	9.1	5.6	3.0	1.2	200
30	SSS5A30S	0.120	10-1/2	11	4-1/2	5	3/4 x 25 x 3	260	1.8				200
30	SSS5M30S	0.188	10-1/2	11	4-1/2	5	3/4 x 25 x 3	392	9.6	5.9	1.9	0.2	200
30	SSS6A30S	0.120	12-1/2	12-1/2	5	6	1 x 36 x 4	330	4.1	1.3			200
30	SSS6M30S	0.188	12-1/2	12-1/2	5	6	1 x 36 x 4	489	18.5	12.5	8.4	5.3	200
35	SSS5M35S	0.188	10-1/2	11	4-1/2	5	3/4 x 25 x 3	453	5.5	2.4			200
35	SSS6M35S	0.188	12-1/2	12-1/2	5	6	1 x 36 x 4	564	11.8	7.0	3.5	1.0	200
35	SSS6X35S	0.250	12-1/2	12-1/2	5	6	1 x 36 x 4	738	16.0	10.5	6.4	3.4	200
39	SSS6M39S	0.188	12-1/2	12-1/2	5	6	1 x 36 x 4	618	7.0	2.4	-		300
39	SSS6X39S	0.250	12-1/2	12-1/2	5	6	1 x 36 x 4	816	12.0	6.7	3.0	0.5	300

NOTES:

- NOTES:

 1. Catalog number includes pole with hardware kit. Anchor bolts not included. Before installing, make sure proper anchor bolts and templates are obtained from Eaton's Cooper Lighting business.

 2. Tenon size or machining for rectangular arms must be specified. Hand hole position relative to drill location.

 3. Shaft size, base square, anchor bolts and projections may vary slightly. All dimensions nominal.

 4. EPAs based on shaft properties with wind normal to flat. EPAs calculated using base wind velocity as indicated plus 30% gust factor.